



# Order Form: Barwon & Hudson Lift Chair

Prepared by Client Name Order Date Reference No.

Circle required dimensions and configurations

Mechanism Single Motor (Standard) Dual Motor 180kg Dual Motor RC Electric Recline RC Manual Recline RC

## CONFIGURATION

	J	,	2442 110		ŭ							
Whee	els 50mm Cast	50mm Castors (Standard)		75 Mobile Castors (+25mm Seat height)			Glides			Remove Castors		
Memory Fo	oam Sea	at	Legrest		Backrest		Armrest			Hygroflex		
Back Cushion Option	ons Gluteal	Gluteal Recess		Concave Back B		ow-fill Lumbar		Comfort Pack		Heat & Massage		
Cushion Inse	ert None (Stan	None (Standard) 18x16		Low Profile 18x16 High		16x16 Low Profile		16x16 High Prof		file Include Infill Plug		
Controller Opti	ion Right (S	Right (Standard)		Left		ocket Joyst		ck	Controller Loop L		Left/Right	
Back Ang		Standard			Vertical			Over-Vertical				
Other Option		Waterfall Arms			Scotch Guard			Flush Front				
other optic								eq rest Side Walls				
		Tablet Arm Left/Right (default						- C				
		chair cover				Loose armr	Loose armrest/headrest covers			Fitted armrest/headrest covers		
	Removable	Removable Headrest A B C D E (please circle one)						Full Battery Backup				
										DIMEN	NSIONS	
	Seat	Seat	Bac		Footre		pular	Seat		Arm	Seat	
	νερτη (mm)	Depth Height (mm)		ht )	Lengti (mm)	Length He (mm) (		Width (mm)		Height (mm)	Foam (mm)	
	-100 CP -150 CP	-30 RC	-120cp -150	ACP _ 180 CP	-50			-150		-60		
Decrease Size	-25 -50 -75	-25	-30 CP -60		-25			-50 -100		-30	-20	
Mini Standard Size	455	456	63	6	N/A	4	29	540		199	N/A	
Increase Size	+25 +50	+20	+30 +60	+90	+25			+50		+30	+20	
Therease Size	+75		+120	+150 DM	+50					+60		
	-100 -150cp	-30 RC	-120cp -150	1CP - 180 CP	- 50			-150		-60		
Decrease Size	-25 -50 -75	-25	-30 -60 CP -90 CP		-25			-50 -100		-30	-20	
A Standard Size	490	476	64	7	N/A	4	40	540		180	N/A	
Increase Size	+25 +50	+20	+30 +60	+90	+25			+50		+30	+20	
11101 0400 0120	+75		+120 DM	+150 DM	+50					+60		
	-100 -150cp	-30 RC	-120cp -150	)CP -180CP	-50			-150		-60		
Decrease Size	-25 -50 -75	-25	-30 -60		-25			-50 -	100	-30	-20	
B Standard Size	520	496	68	8	N/A	4	81	540		190	N/A	
Increase Size	+25	+25	+30 +60	DM +90 DM	+25			+50		+30	+20	
2.10.1 04.00 02.20	+50		+120 DM	+150 DM	+50					+60		
	-100 -150	-30 RC	-120°P -150	CP - 180 CP	-50			-150		-60		
Decrease Size	-25 -50 -75	-25	-30 -60		-25			-50 -	100	-30	-20	
C Standard Size	545	546	71	8	N/A	5	11	540		190	N/A	
Increase Size	+25	+25	+30 DM	+60 DM	+25			+50		+30	+20	
		+50	+90 DM	+120 DM	+50					+60		

NOTE: Reduced seat foam limits Safe working load to 90kg and reduces seat foam warranty to 2 years.

COLOUR AND FINISH

Fabric Outer

Show wood Walnut Mahogany Baltic Teak Remove Show Wood


ADDITIONAL NOTES





# Chair Sizing

#### OUR RECOMMENDED STARTING POINT



C	5′11+	180cm+
В	5'8 to 5'11	172 to 180cm
Α	5'2 to 5'8	157 to 172cm
Mini	4'10 to 5'2	147 to 157cm

## **ENSURING CORRECT MODIFICATIONS**



- Heels up against the footrest
- Light pressure on the calf
- Feet planted on the ground, avoid legs angled too far forward
- Mention gluteal recess if user unable to sit back into the chair



- Nape of the neck sitting in centre of top cushion
- Shoulder blades sitting in gap of the top roll
- Adjustments can be made manually by repositioning backrest



- Knees in line with hips
- Feet planted on the ground
- Even pressure from their backside to the back of their legs
- Use blocks to determine adjustment if feet don't reach the ground



4m Height

- Elbow to wrist should be supported
- If shoulders are hunched up, arms too high
- Gap between armrest and elbow, arms too low



- Fit a fist beside each thigh comfortably
- Waterfall arms can also decrease seat width



- Heel clear of footrest to avoid pressure sores
- Ankles to be supported

